

### *SPECIAL CLAMP*

#### *Mounting adaptor for the TinyMike (ATM216)*



The mounting adaptor (ATHPD) serves to adapt the diameter of the TinyMike (ATM216) to camera's microphone bracket.

One to two layers of the supplied foam rubber build up the diameter.

Start and end the foam rubber near the slit. For most Sony cameras one layer, for most Panasonic two layers are sufficient.

When done, insert the cable through the barrel adaptor and plug it into the microphone. Then insert the TinyMike (ATM216) into the adaptor (ATHPD).



experience quality.

**Ambient Recording GmbH**

Schleissheimer Straße 181 c | DE - 80797 Munich  
vox +49 89 36055100 | fax +49 89 6518558 | info@ambient.de | www.ambient.de/en

**MADE IN GERMANY**

© 2019, Ambient Recording GmbH